

>>> **EMERGENCY EYEWASH**



**10 SECOND RUSH.  
15 MINUTE FLUSH.**

**FENDALL PURE FLOW 1000®**

**EMERGENCY EYEWASH STATION**

**Available with  
standard or  
100% sterile  
saline eyewash  
solution.**

**Is Your Facility in Compliance with Current Emergency Eyewash Regulations?** OSHA and the American National Standards Institute specify requirements for workplace eye hazard areas. In fact, ANSI Z358.1 states that primary, 15-minute eyewash units “shall be in accessible locations that require no more than 10 seconds to reach.”

The Fendall Pure Flow 1000 emergency eyewash station delivers the required 15 minutes of flushing with a preserved, buffered, saline solution that is superior to tap water for emergency eye care. Completely self-contained, the Fendall Pure Flow 1000 uses sealed fluid cartridges and provides affordable, portable placement within 10 seconds of any work-place hazard. No plumbing required! Available with standard or **100% sterile** saline eyewash solution.

### FENDALL PURE FLOW 1000

The Fendall Pure Flow 1000 emergency eyewash station delivers unequaled eyewash safety, reliability, and value. The patented system delivers contaminant-free and physiologically correct saline solution from factory-sealed cartridges.

#### FEATURES AND BENEFITS

- **Self-contained/no plumbing.** Easy installation with no plumbing required. Can be easily and affordably placed near most workplace hazards or transported with optional universal cart or stand.
- **Factory-sealed fluid cartridges.** Eliminates mixing, measuring, and the opportunity for airborne particles or microorganisms to contaminate the fluid prior to use.
- **Saline solution delivery.** Unique nozzle design delivers a soft “ribbon” of a preserved, buffered, saline solution superior to tap water for emergency eye care. **A 100% sterile saline option is also available.**
- **Constant flow rate.** Permits thorough flushing with a constant flow rate and stream height that provides 0.4 gpm for entire 15-minute cycle required by ANSI Z358.1-2009.
- **Integral fluid reservoir.** Captures waste fluid to eliminate spill hazards and simplify fluid disposal.
- **Easy cartridge replacement.** Cartridges remain sealed until activated. Expiration date is included on activation straps – and cartridge replacement takes less than five minutes.
- **Easy maintenance.** ESP RFID technology gives you instant, accurate safety information about the cartridges while the easy view window makes inspection and maintenance quick and easy
- **Easy installation.** Instruction manual, video and cartridge components ensure proper installation and maintenance to prevent false activation.

#### No Plumbing Required

The Fendall Pure Flow 1000 does not require costly plumbing for affordable, portable placement near most workplace hazards. Patented design delivers a constant flow rate and stream height, and provides 0.4 gpm for 15 minutes as required by ANSI Z358.1-2009. A unique fluid pressure balancing system and nozzles maximize comfort with a soft “ribbon” of saline solution.



#### Sealed Fluid Cartridges Now with Sterile Option!

The Fendall Pure Flow 1000 uses a sealed cartridge design that eliminates mixing, measuring, and the opportunity for airborne particles or microorganisms to contaminate the fluid prior to use. Factory-sealed cartridges feature an integral nozzle and hose design to ensure delivery of purified, contaminant-free, and physiologically correct saline solution.



#### Low Maintenance Featuring ESP™ Enabled Safety Products RFID Technology!

Cartridges remain sealed until activated and changes take less than five minutes. An integral reservoir captures waste fluid, simplifying disposal. Easy-to-read warnings show service requirements, saving maintenance and inspection time. ESP RFID technology makes maintenance and inventory control even easier. Sperian saline cartridges last at least four times longer than other self-contained systems.\*



\*Shelf life determined by date of manufacture.  
Always check product expiration date.

#### ORDERING INFORMATION

Model#	Description	Shipping Dimensions	Weight
32-001000-0000	Fendall Pure Flow 1000 Eyewash Station	29" x 18" x 31"	38 lbs.
32-001050-0000	Refill Cartridges (Set of 2)	23.5" x 12.5" x 11.5"	70 lbs.
32-ST1050-0000	Sterile Refill Cartridges (Set of 2)	23.5" x 12.5" x 11.5"	70 lbs.
32-001060-0000	Universal Cart	31" x 10.5" x 29"	54 lbs.
32-001065-0000	Universal Stand	60.5" x 30" x 1.5"	27 lbs.

Sperian Protection Americas, Inc.  
900 Douglas Pike, Smithfield, RI 02917-1874 | tel: 1.800.fendall